

**Adapter**  
**NPFV-AF-G14-N14-MF**  
Part number: 563397



**Data sheet**

| Feature                        | Value                                                              |
|--------------------------------|--------------------------------------------------------------------|
| Nominal size                   | 6 mm                                                               |
| Operating pressure             | 0.2 MPa...0.8 MPa<br>2 bar...8 bar                                 |
| Explosion protection           | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class CRC | 1 - Low corrosion stress                                           |
| LABS (PWIS) conformity         | VDMA24364 zone III                                                 |
| Pneumatic connection, port 1   | G1/4                                                               |
| Pneumatic connection, port 2   | 1/4 NPT                                                            |
| Note on materials              | RoHS-compliant                                                     |
| Material adapter               | High-alloy stainless steel                                         |
| Material seals                 | NBR                                                                |