


**Axial kit**  
**EAMM-A-P8-38A-70A**  
Part number: 564996



**Data sheet**

| Feature                        | Value                  |
|--------------------------------|------------------------|
| Nominal length                 | 13.75 mm               |
| Mounting position              | optional               |
| Max. rotational speed          | 8000 rpm               |
| LABS (PWIS) conformity         | VDMA24364-B2-L         |
| Storage temperature            | -25 °C...60 °C         |
| Relative air humidity          | 0 - 95%                |
| Degree of protection           | IP40                   |
| Ambient temperature            | -10 °C...60 °C         |
| Mass moment of inertia         | 5.87 kgmm <sup>2</sup> |
| Transmittable torque           | 12.5 Nm                |
| Product weight                 | 200 g                  |
| Interface code, actuator       | P8-38A                 |
| Interface code, motor in       | 70A                    |
| Interface code, clutch housing | 38A                    |
| Note on materials              | RoHS-compliant         |