

Silencer
U-3/4-B-NPT
Part number: 566823

FESTO



Data sheet

Feature	Value
Mounting position	optional
Operating pressure complete temperature range	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Flow rate to atmosphere	11834 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:~:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	81 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	128 g
Pneumatic connection	3/4 NPT
Material shock absorber insert	PE
Material screwed plug	Aluminium
Note on materials	RoHS-compliant
Material housing	Aluminium