

Push-in connector NPQM-D-Q14-E-P10

Part number: 570452

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	13 mm
Design	Straight design Push-pull principle
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...70 °C
Product weight	47.4 g
Pneumatic connection, port 1	For tubing outer diameter of 14 mm
Pneumatic connection, port 2	For tubing outside diameter of 14 mm
Colour of release ring	Silver
Note on materials	RoHS-compliant
Material housing	Brass, nickel-plated
Material tubing seal	NBR