


Power supply module VMPAL-SP

Part number: 570774

FESTO



Data sheet

Feature	Value
Width	23.2 mm
Length	107.3 mm
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure	0.3 MPa...0.8 MPa 3 bar...8 bar
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	50 g
Pneumatic connection, port 1	For 20 mm cartridge
Note on materials	RoHS-compliant
Material supply module	Wrought aluminium alloy PA-reinforced