


# Time delay valve VZO-3-PK-3

Part number: 5754

FESTO



## Data sheet

Feature	Value
Nominal size	2 mm
Type of actuation	Pneumatic
Design	Poppet valve with spring return
lap	Underlap
Note on forced dynamization	Switching frequency min. 1/week
Operating pressure	2.5 bar...8 bar
Standard nominal flow rate (standardised to DIN 1343)	60 l/min
Adjustable delay time	0.25 s...5 s
Pause duration for reset	50 ms
Repetition accuracy of time setting	± 0.5 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...60 °C
Product weight	150 g
Type of mounting	Front panel mounting On mounting frame Either:
Pneumatic connection	PK-3
Material housing	Die-cast zinc