


# Time delay valve VZ-3-PK-3

Part number: 5755

**FESTO**



## Data sheet

Feature	Value
Nominal size	2 mm
Type of actuation	Pneumatic
Design	Poppet valve with spring return
lap	Underlap
Note on forced dynamization	Switching frequency min. 1/week
Operating pressure	2.5 bar...8 bar
Standard nominal flow rate (standardised to DIN 1343)	90 l/min
Adjustable delay time	0.25 s...5 s
Pause duration for reset	55 ms
Repetition accuracy of time setting	± 0.5 s
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...60 °C
Product weight	150 g
Type of mounting	Front panel mounting On mounting frame Either:
Pneumatic connection	PK-3
Material housing	Die-cast zinc