

Common supply manifold VABM-B10-20-G38-7-P53

Part number: 576368

FESTO



Data sheet

Feature	Value
Grid dimension	22 mm
Mounting position	optional
Max. number of valve positions	7
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	437 g
Type of mounting	Via mounting bracket
Pneumatic connection, port 1	G3/8
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy