

Plug screw **NPQH-BK-G18-P10** Part number: 578406

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | optional |
| Design | Plug screw |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa...2 MPa -0.95 bar...20 bar -13.775 psi...290 psi |
| Note on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Certificate issuing authority | NSF C0523185 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:::] Water (liquid, ice-free) |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Suitable for use with food | See declaration of conformity NSF/ANSI 169 |
| Ambient temperature | 0 °C...150 °C |
| Nominal torque | 6 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 4.4 g |
| Type of mounting | Internal hexagon, size 5 mm |
| Pneumatic connection, port 1 | Male thread G1/8 |
| Note on materials | RoHS-compliant |
| Material housing | Brass, chemically nickel-plated |
| Material thread seal | FPM |
| Material release ring | Brass, chemically nickel-plated |