


Elbow quick connector GCK-1/8-PK-4-KU

Part number: 6267

FESTO



Data sheet

Feature	Value
Nominal size	2.9 mm
Mounting position	optional
Design	L-shape
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	Male thread R1/8
Pneumatic connection, port 2	For tubing outside diameter of 6 mm For barbed fitting inside diameter of 4 mm with nut
Material union nut	POM
Material screwed plug	POM
Note on materials	RoHS-compliant