

# Centring sleeve ZBH-25

Part number: 8023856

FESTO



## Data sheet

Feature	Value
Size	25
Mounting position	optional
Size of pack	10
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-25 °C...60 °C
Note on materials	RoHS-compliant
Material sleeve	High-alloy stainless steel