

Manifold block

VABM-B10-30S-G12-8

Part number: 8026383

FESTO



Data sheet

Feature	Value
Grid dimension	32 mm
Mounting position	optional
Max. number of valve positions	8
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	2285 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 5	G1/2
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy