

Manifold block
VABM-B10-30S-N12-4
Part number: 8026388

FESTO



Data sheet

Feature	Value
Grid dimension	32 mm
Mounting position	optional
Max. number of valve positions	4
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1267 g
Type of mounting	With through-hole
Pneumatic connection, port 1	1/2 NPT
Pneumatic connection, port 3	1/2 NPT
Pneumatic connection, port 5	1/2 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy