


Solenoid coil VACN-N-A1-1-EX2-N

Part number: 8029136

FESTO



Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Duty cycle	100%
Insulation material class	F
Insulation material class of enamelled wire	H
Characteristic coil data	24 V DC: 2.1 W
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gc (GB)
Explosion protection	Zone 2 (ATEX) Zone 2 (UKEX) Zone 22 (ATEX) Zone 22 (UKEX)
Certificate issuing authority	DNV TAA000011J
ATEX category gas	II 3G
ATEX category dust	II 3D
Explosion ignition protection type for gas	Ex nA IIC T5/T4 X Gc
Explosion ignition protection type for dust	Ex tc IIIC T95°C/T105°C X Dc
Explosion ambient temperature	-20°C ≤ Ta ≤ +60°C
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C...60 °C
Product weight	95 g
Electrical connection	Type A To DIN EN 175301-803
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material housing	Polymer Steel

Feature	Value
Material electrical contact	Brass
Material winding	Copper