

T-fitting
NPFC-T-G18-2R18-FMM
Part number: 8030255

FESTO



Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Size of pack	10
Operating pressure	-0.95 bar...50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...150 °C
Product weight	23.1 g
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	R1/8
Note on materials	RoHS-compliant