

Manifold sub-base VABV-S1-1HSB-G38

Part number: 8030650

FESTO



Data sheet

Feature	Value
Construction width	44 mm
Exhaust-air function	With flow control option
Based on standard	ISO 5599-1
Max. number of valve positions	1
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Suitability for vacuum	yes
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Media temperature	-10 °C...50 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...50 °C
Product weight	490 g
Pneumatic connection, port 2	G3/8
Pneumatic connection, port 4	G3/8
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium