


End plate VABE-S1-1RZ-N12

Part number: 8032669

FESTO



Data sheet

| Feature | Value |
|------------------------------------|--|
| Construction width | 44 mm |
| Exhaust-air function | With flow control option |
| Based on standard | ISO 5599-1 |
| Operating pressure | -0.09 MPa...1.6 MPa -0.9 bar...16 bar |
| Suitability for vacuum | yes |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C...60 °C |
| Media temperature | -10 °C...50 °C |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C...50 °C |
| Product weight | 410 g |
| Type of mounting | Via through-hole for M6 screw |
| Pilot air port 12/14 | 1/4 NPT |
| Pneumatic connection, port 1 | 1/2 NPT |
| Pneumatic connection, port 3 | 1/2 NPT |
| Pneumatic connection, port 5 | 1/2 NPT |
| Note on materials | RoHS-compliant |
| Material end plate | Die-cast aluminium |