

**Sub-base**  
**VMPA1-FB-AP-4-1-S1-RV**  
Part number: 8034551

**FESTO**



**Data sheet**

| Feature                        | Value                                     |
|--------------------------------|-------------------------------------------|
| Width                          | 50 mm                                     |
| Length                         | 107.3 mm                                  |
| Grid dimension                 | 10.5 mm                                   |
| Max. number of valve positions | 4                                         |
| Operating pressure             | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar    |
| Pilot pressure                 | 0.3 MPa...0.8 MPa<br>3 bar...8 bar        |
| Operating medium               | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class CRC | 0 - No corrosion stress                   |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                         |
| Ambient temperature            | -5 °C...50 °C                             |
| Product weight                 | 190 g                                     |
| Note on materials              | RoHS-compliant                            |
| Material sub-base              | Die-cast aluminium                        |