

Supply plate VABF-S1-1-P1A11-G12

Part number: 8037655

FESTO



Data sheet

| Feature | Value |
|---|--|
| Construction width | 44 mm |
| Exhaust-air function | Via throttle plate |
| Based on standard | ISO 5599-1 |
| Max. number of valve positions | 1 |
| Operating pressure | 0 MPa...1 MPa 0 bar...10 bar |
| Suitability for vacuum | yes |
| CE mark (see declaration of conformity) | To EU Low Voltage Directive |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C...60 °C |
| Media temperature | -10 °C...50 °C |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C...50 °C |
| Product weight | 660 g |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 3 | G1/2 |
| Pneumatic connection, port 5 | G1/2 |
| Material exhaust plate | Wrought aluminium alloy |
| Note on materials | RoHS-compliant |
| Material supply plate | Die-cast aluminium |