


# Cabinet through feed NEFU-D12G4-D12DG4

Part number: 8040459

FESTO



## Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101
Type of mounting	Screw-clamped
Electrical connection 1	Straight socket, M12x1, 4-pin, D-coded
Electrical connection 2	Straight socket, M12x1, 4-pin, D-coded
Operational voltage range DC	0 V...30 V
Current rating at 40° C	4 A
Immunity to surge	0.8 kV
Transmission characteristics	In accordance with category 5, EN 50173, class D In accordance with category 5, ISO/IEC 11801, class D
Degree of protection	IP65 IP67
Ambient temperature	-25 °C...85 °C
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	Brass, nickel-plated
Housing colour	Silver
Material electrical contact	Brass Bronze