

Fixed flow restrictor VFFG-T-F6-11

Part number: 8047356

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Type of mounting	Tapped
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Ambient temperature	-5 °C...60 °C
Approval	c UL us - Recognized (OL)
Size	For ø 5.8 mm
Nominal size	1.15 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Product weight	1.2 g
Note on materials	RoHS-compliant