

Common supply manifold OABM-P-G3-15-2

Part number: 8049144

FESTO



Data sheet

Feature	Value
Number of device positions	2
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque	3.3 Nm
Min. tightening torque	0.3 Nm
Product weight	59.6 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/8
Note on materials	RoHS-compliant
Material sub-base	Wrought aluminium alloy