

**Cover kit**  
**VAVC-F12-SCC-40-TP**  
 Part number: 8084032

**FESTO**



**Data sheet**

Feature	Value
Nominal size DN	40
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364 zone III
Medium	Vapour Mineral oil-based hydraulic fluid Inert gases Mineral oil Water Filtered compressed air, grade of filtration 200 µm Neutral fluids
Note on the medium	Gaseous media are only permitted with inflow via valve seat.
Media temperature	-30 °C...200 °C
Ambient temperature	0 °C...60 °C
Storage temperature	-10 °C...60 °C
Mounting position	optional
Product weight	846 g
Note on materials	RoHS-compliant
Material cover	High-alloy stainless steel
Material spindle seal	PTFE
Material seat seal	PTFE, modified