


Pressure gauge PAGN-26-10-G18S

Part number: 8088985

FESTO



Data sheet

Feature	Value
Indicating range	0 bar...10 bar
Nominal size of pressure gauge	26
Design	Bourdon tube pressure gauge
Type of mounting	In-line installation
Operating medium	Inert gases Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Alternating load factor	0.66
Measurement accuracy class	4
Degree of protection	IP43
Storage temperature	-5 °C...50 °C
Media temperature	-5 °C...50 °C
Ambient temperature	-5 °C...50 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	G1/8 with sealing ring
Material in contact with the medium	ABS Brass
Material screwed plug	ABS
Material housing	ABS
Material screen	PS
Housing colour	Black
Product weight	8 g
Scale	Double scale Bar (outside scale) psi (inner scale)