

Fitting

NLFA-D-U14-B2.1-PP-P10

Part number: 8104289

FESTO



Data sheet

Feature	Value
Size of pack	10
Design	Tubing mount via barbed connector Straight design
Size	ø 8 mm
Fluid connection	UNF1/4-28
Fluid connection 2	For tubing I.D. 2.1 mm
Medium	Liquid media Gaseous media
Note on the medium	Observe resistance of materials that come into contact with the media
Operating pressure complete temperature range	-0.075 MPa...0.4 MPa -0.75 bar...4 bar -10.875 psi...58 psi
Media temperature	0 °C...35 °C
Ambient temperature	0 °C...35 °C
Storage temperature	-20 °C...70 °C
Sealing principle	Hard
Mounting position	optional
Nominal torque	15 Ncm
Tolerance for nominal tightening torque	± 15%
Product weight	0.5 g
Material in contact with the medium	PP
Material screwed plug	PA-reinforced
Note on materials	RoHS-compliant
Suitable for use with food	See supplementary material information
LABS (PWIS) conformity	VDMA24364 zone III
Instructions on use	See application note (available on the Support Portal at festo.com)