

Manifold block VABS-C12-6-B-M3

Part number: 8122793

FESTO



Data sheet

Feature	Value
Construction width	20 mm
Mounting position	optional
Design	Connection direction downwards
Max. number of valve positions	1
Operating pressure	-0.1 MPa...0.7 MPa -1 bar...7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:1]
Note on operating and pilot medium	Maximum particle size 5 µm
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C...50 °C
Product weight	13.5 g
Type of mounting	With through-hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M3
Pneumatic connection, port 3	M5
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy