

# Manifold block

## VABM-C12-6M-M5-M3-10

Part number: 8122794

FESTO



### Data sheet

Feature	Value
Construction width	20 mm
Mounting position	optional
Design	Connection direction downwards
Max. number of valve positions	10
Operating pressure	-0.1 MPa...0.7 MPa -1 bar...7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:1]
Note on operating and pilot medium	Maximum particle size 5 µm
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C...50 °C
Product weight	49.5 g
Type of mounting	With through-hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M3
Pneumatic connection, port 3	M5
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy