

Cable fitting NETC-M20-PBK-T14

Part number: 8151590

FESTO



Data sheet

Feature	Value
Ambient temperature	-40 °C...100 °C
Degree of protection	IP66 IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
Size	M20x1.5
Cable diameter	4 mm...13 mm
Colour	Black
Material cable gland	PA
Material seals	EPDM
Product weight	14 g
Size of pack	1
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant