


Connection kit
DADG-AK-G8-25-30
Part number: 8152398

FESTO



Data sheet

Feature	Value
Size	25
Stroke	30 mm
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque	5 Nm
Tolerance for tightening torque	±10%
Max. tightening torque pneumatic connection 1	3 Nm
Product weight	44.8 g
Pneumatic connection	G1/8
Material adapter	Epoxy resin
Material seals	FPM
Material screws	Coated steel