

Plastic tubing
PUN-H-F-16X2,5-RT
Part number: 8153420

FESTO



Data sheet

| Feature | Value |
|---|--|
| Outside diameter | 16 mm |
| Flow-relevant bending radius | 88 mm |
| Inside diameter | 11 mm |
| Min. bending radius | 38 mm |
| Instructions on use | Tubing without printing TPE-U Ether based |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure complete temperature range | -0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi |
| Temperature-dependent operating pressure | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Note on operating pressure | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60 °C |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:...] Water (liquid, ice-free) |
| Fire test material | UL94 HB |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Suitable for use with food | See declaration of conformity |
| Ambient temperature | -35 °C...60 °C |
| Product weight according to length | 0.122 kg/m |
| Pneumatic connection | For push-in connector O.D. 16 mm |
| Colour | Red |
| Shore hardness | D 52 +/-3 |
| Note on materials | RoHS-compliant |
| Material tubing | TPE-U(PU) |