

Cartridge NPQX-D-PC10-T14-P10

Part number: 8184510

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal size | 4.5 mm |
| Tubing insertion depth | 11.93 mm |
| Type of seal on screwed plug | No seal |
| Mounting position | Horizontal |
| Design | Straight design Push-pull principle |
| Size of pack | 10 |
| Operating pressure | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Operating pressure complete temperature range | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 2.15 g |
| Type of mounting | Via retaining clamp |
| Pneumatic connection, port 1 | Cartridge 10 mm |
| Pneumatic connection, port 2 | For tubing outside diameter of 1/4" |
| Colour of release ring | Blue |
| Note on materials | RoHS-compliant |
| Material housing | PA-reinforced |