

Manifold block VABS-P4-8S-M5

Part number: 8186785

FESTO



Data sheet

Feature	Value
Construction width	12 mm
Mounting position	optional
Design	Connection direction at side
Max. number of valve positions	1
Operating pressure	0 bar...10 bar
Operating medium	Inert gases Air
Note on operating and pilot medium	Lubricated operation not possible Maximum particle size 10 µm
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C...80 °C
Media temperature	5 °C...50 °C
Ambient temperature	5 °C...50 °C
Product weight	40 g
Type of mounting	With through-hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Note on materials	RoHS-compliant
Material sub-base	Anodised wrought aluminium alloy