


## Sub-base VABS-K2-12S-20-G18-P

Part number: 8186871

**FESTO**



## Data sheet

Feature	Value
Size	12
Nominal size	2 mm
Valve size	12 mm
Fluid connection	Female thread G1/8
Mounting position	optional
Design	Connection direction at side
Max. number of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Note on operating and pilot medium	Observe resistance of materials that come into contact with the media
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...70 °C
Suitable for use with food	See supplementary material information
Media temperature	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Max. tightening torque for valve mounting	0.33 Nm
Max. tightening torque for fitting	7 Nm
Max. tightening torque	0.6 Nm
Product weight	31 g
Mounting method for sub-base	With through-hole
Mounting method for valve	Via female thread
Note on materials	RoHS-compliant
Material sub-base	PEEK