

Round cylinder DPRA-N-1 1 1/2"-5-ME-N

Part number: 8217877

FESTO



Data sheet

Feature	Value
Stroke	5 in
Piston diameter	1 1/2"
Piston rod thread	7/16-20 UNF-2A
Cushioning	No cushioning
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod Cylinder barrel
Position detection	Without
Protection against torque/guide	Round piston rod
Operating pressure	9.99 psi...150 psi
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-40 °F...300 °F
Product weight	1.1 lb
Pneumatic connection	1/8 NPT
Note on materials	RoHS-compliant
Material seals	NBR
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel