


Axial kit EAMM-A-D60-90R

Part number: 8234794



Data sheet

Feature	Value
Nominal length	75 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	21 Nm
Product weight	1080 g
Interface code, actuator	D60
Interface code, motor in	90R 92RA
Note on materials	RoHS-compliant