


Vacuum generator VAD-1/4

Part number: 9394

FESTO



Data sheet

Feature	Value
Nominal size, Laval nozzle	1 mm
Mounting position	optional
Ejector characteristic	High vacuum
Design	T-shape
Operating pressure	0.15 MPa...1 MPa 1.5 bar...10 bar 21.75 psi...145 psi
Max. vacuum	80 %
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-20 °C...80 °C
Ambient temperature	-20 °C...80 °C
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Vacuum connection	G1/4
Material housing	Die-cast aluminium