


# Pressure indicator OH-8-GN

Part number: 10089

FESTO



## Data sheet

| Feature                            | Value   |
|------------------------------------|---|
| Operating pressure MPa             | -0.1 ... 0.8 MPa  |
| Working pressure                   | -1 ... 8 bar  |
| Operating pressure                 | -14.5 ... 116 psi   |
| Operating medium                   | Compressed air in accordance with ISO8573-1:2010 [7::-:]                    |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity                    | VDMA24364-B1/B2-L   |
| Ambient temperature                | -10 ... 60 °C   |
| Pneumatic connection               | Barbed fitting PK-3   |
| Materials note                     | Conforms to RoHS  |