

DUO plastic tubing PU-3-DUO-BS

Part number: 11958

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).
The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	4.4 mm
Bending radius relevant for flow rate	14 mm
Inside diameter	2.9 mm
Temperature dependent working pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:]
Ambient temperature	-35 ... 60 °C
Authorization	TÜV
Product weight according to length	0.0192 kg/m
Color	blue/black
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-U(PU)