


# Silencer AMTE-M-H-G18

Part number: 1206622

★ Core product range

FESTO

Suitable for reducing noise at the exhaust ports of pneumatic systems.



## Data sheet

| Feature                                 | Value  |
|---|--|
| Assembly position                       | Any  |
| Container size                          | 20   |
| Operating pressure MPa                  | 0 ... 1 MPa  |
| Working pressure                        | 0 ... 10 bar   |
| Flow rate to atmosphere                 | 615 l/min  |
| Operating medium                        | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium      | Lubricated operation possible                            |
| Corrosion resistance classification CRC | 1 - Low corrosion stress                                 |
| PWIS conformity                         | VDMA24364-B1/B2-L  |
| Sound pressure level                    | 92 dB(A)   |
| Ambient temperature                     | -40 ... 80 °C  |
| Product weight                          | 5 g  |
| Pneumatic connection                    | G1/8   |
| Material of silencer insert             | Bronze   |
| Material of threaded plug               | Brass  |
| Materials note                          | Conforms to RoHS   |