

Plastic tubing PU-13-SW

Part number: 12133

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).
The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	17.6 mm
Bending radius relevant for flow rate	83 mm
Inside diameter	13 mm
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.133 kg/m
Pneumatic connection	for barbed connector internal diameter 13 mm with nut
Color	Black
Shore hardness	A 86 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)