


# Solenoid coil

## MSN1W-230AC-OD

Part number: 123062

FESTO

For AC voltage, without socket.



## Data sheet

Feature	Value
Assembly position	Any
Min. pickup time	10 ms
Duty cycle	100 %
Power factor cos {phi}	0.7
Characteristic coil data	230 V AC: 50 Hz, pick-up power 7.5 VA, holding power 5 VA 230 V AC: 60 Hz, pick-up power 5 VA, holding power 3.7 VA
Permissible voltage fluctuation	+/- 10 %
Maritime classification	see certificate
CE symbol (see declaration of conformity)	according to EU low voltage guideline
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
PWIS conformity	VDMA24364-C1-L
Medium temperature	-10 ... 50 °C
Protection class	IP65
Ambient temperature	-10 ... 50 °C
Product weight	80 g
Electrical connection	3-pin Plug pattern type A to EN 175301-803 Per DIN EN 175301-803
Mounting type	Clamped with retaining clamp with accessories
Material housing	PA
Material electrical contact	Steel
Material winding	Copper