


Subbase VABS-C8-12XB-QX-D

Part number: 1236029

Classic - do not use for new projects

FESTO

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Width	24 mm
Max. number of valve positions	1
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque, valve mounting	0.48 ... 0.72 Nm
Max. tightening torque, wall mounting	1.3 Nm
Product weight	30 g
Auxiliary pilot air port 12/14	prepared for cartridge
Pneumatic connection, port 1	Prepared for cartridge
Pneumatic connection, port 3	Prepared for cartridge
Pneumatic connection, port 5	Prepared for cartridge
Materials note	Conforms to RoHS
Material manifold	Reinforced PA