

Cartridge QSPLKG20-10

Part number: 132856

FESTO

With push-in connector, L-form



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 6.1 mm |
| Type of seal on screw-in stud | O-ring |
| Assembly position | Any |
| Design | L-shape |
| Container size | 10 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | -0.095 ... 1 MPa |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating pressure for entire temperature range | -13.775 ... 145 psi |
| Maritime classification | see certificate |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 ... 60 °C |
| Product weight | 14 g |
| Mounting type | Mounting pin |
| Pneumatic connection, port 1 | Cartridge 20 mm |
| Pneumatic connection, port 2 | For tubing outside diameter 10 mm |
| color of release ring | blue |
| Materials note | Conforms to RoHS |
| Material housing | PA-reinforced |
| Material release ring | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High alloy steel, non-corrosive |