


Push-in connector QS-V0-4

Part number: 132890

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal size | 2.8 mm |
| Material fire test | UL94 V-0 (housing) UL94 V-0 (releasing ring) |
| Design | Straight design |
| Container size | 1 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | -0.095 ... 1 MPa |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating pressure for entire temperature range | -13.775 ... 145 psi |
| Note on working pressure | Water: max. 0.6 MPa at max. 50°C |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] Water (liquid, free of ice) |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 ... 60 °C |
| Product weight | 6.1 g |
| Pneumatic connection, port 1 | For tubing outside diameter 4 mm |
| Pneumatic connection, port 2 | For tubing outside diameter 4 mm |
| color of release ring | Black |
| Materials note | Conforms to RoHS |
| Material housing | PBT |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High alloy steel, non-corrosive Brass |