

# Coupling EAMC-30-35-8-14

Part number: 1453063

FESTO



## Data sheet

| Feature                | Value                 |
|------------------------|-----------------------|
| Holder diameter 1      | 8 mm                  |
| Holder diameter 2      | 14 mm                 |
| Size                   | 30                    |
| Nominal length         | 35 mm                 |
| Assembly position      | Any                   |
| Max. speed             | 8,000 1/min           |
| PWIS conformity        | VDMA24364-B2-L        |
| Storage temperature    | -25 ... 60 °C         |
| Relative air humidity  | 0 - 95 %              |
| Ambient temperature    | -25 ... 60 °C         |
| Mass moment of inertia | 6.1 kgmm <sup>2</sup> |
| Transferable torque    | 8.2 Nm                |
| Product weight         | 45 g                  |
| Materials note         | Conforms to RoHS      |