

# Clamping sleeve EAMH-86-14-C27.3-P

Part number: 1459337

FESTO



## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 86                     |
| Assembly position      | Any                    |
| Max. speed             | 5,000 1/min            |
| PWIS conformity        | VDMA24364-B2-L         |
| Storage temperature    | -25 ... 60 °C          |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -10 ... 60 °C          |
| Mass moment of inertia | 8.74 kgmm <sup>2</sup> |
| Product weight         | 103 g                  |
| Materials note         | Conforms to RoHS       |