


Swivel flange SNGL-40

Part number: 151528
Product to be discontinued

FESTO

For DNG, DNGU cylinders. Matching clevis foot mounts LSNG, LSNSG.
Type to be discontinued. Available until 2014. See Support Portal for alternative products.



Data sheet

Feature	Value
Size	40
Conforms to standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance classification CRC	2
Ambient temperature	-40 ... 90 °C
Product weight	106 g
Materials note	Free of copper and PTFE
Material information, mounting	Aluminum die cast
Materials information for bearing	Plastic
Screw material data	Steel Galvanized