

# Plastic tubing PAN-10X1,5-SI

Part number: 152701

FESTO

Standard O.D tubing, for QS plug connectors, CN and CK polyamide fittings (not approved for use in the food industry).



## Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	58 mm
Inside diameter	7 mm
Min. bending radius	27 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1.7 MPa
Temperature dependent working pressure	-0.95 ... 17 bar
Temperature-dependent operating pressure	-13.775 ... 246.5 psi
Authorization	TÜV
Maritime classification	see certificate
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-30 ... 80 °C
Product weight according to length	0.042 kg/m
Pneumatic connection	For push-in connector outside diameter 10 mm
Color	silver
Shore hardness	D 55 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-A