

Plastic tubing PU-1/4-B-SW

Part number: 15275

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).

This product is only available if ordered from the Festo Corporation, USA.

The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	6.35 mm
Bending radius relevant for flow rate	22 mm
Inside diameter	4 mm
Temperature dependent working pressure	-0.95 ... 10 bar
Ambient temperature	-30 ... 60 °C
Product weight according to length	0.024 kg/m
Color	Black