


Push-in sleeve

QSH-3/16-U

Part number: 153818

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Assembly position | Any |
| Design | Straight design |
| Container size | 1 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | -0.095 ... 1 MPa |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating pressure for entire temperature range | -13.775 ... 145 psi |
| Maritime classification | see certificate |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7::-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 1 g |
| Pneumatic connection, port 1 | Push-in sleeve diameter 3/16" |
| Pneumatic connection, port 2 | Push-in sleeve diameter 3/16" |
| Ambient temperature Fahrenheit | 14 ... 140 °F |
| color of release ring | Grey |
| Materials note | Conforms to RoHS |
| Material housing | PBT |